

Cerniera Clip-on - Braccio regolabile per anta in alluminio

Clip-on hinge - Adjustable arm for aluminium frame



SMART C50 CLIP-ON 110°

Collo "0"
Sormonto fino 18 mm.


Crank "0"
Full overlay application (up to 18 mm)

C50A430.10

← 200




Aluminum frame



$H = -14 + K - D$

D	K	3	4	5	6	7
H	1	18	19	20	21	
2	15	16	17	18	19	
4	13	14	15	16	17	

Lavorazione montaggio
Assembly process






SMART C50 CLIP-ON 110°

Collo "9"
Sormonto fino 11 mm.

Crank "9"
Half overlay application (up to 11 mm)

C50B430.10


← 200



$H = 4 + K - D$

D	K	3	4	5	6	7
H	0	7	8	9	10	11
2	5	6	7	8	9	
4	3	4	5	6	7	

Lavorazione montaggio
Assembly process



Cerniera Clip-on - Braccio regolabile per anta in alluminio

Clip-on hinge - Adjustable arm for aluminium frame

SMART C50 CLIP-ON 110°


Collo "18"

Per ante interne



Crank "18"

Insert application

← 200




C50C430.10






$$H=4+K-A$$

A \ K	3	4	5	6	7
0	1	0	-1	-2	-3
2	3	2	1	0	-1
4	5	4	3	2	1

Lavorazione montaggio
Assembly process



Schema di foratura - Drilling diagram



Schema di montaggio - Assembly sequence

